


Section: 2010

Bulletin: 1030

Issued:06/2010

Mounting Options





Standard Wall Mounting

Lag bolts and anchors provided by customer for securing to an existing vertical surface.

Optional Pedestal Mounting

Floor mounted unit; Stainless steel cover, box and tube; Ideal where floor piping is accessible. All water and steam piping is concealed.






Optional Recessed Wall Mixing Unit Enclosure

Mixing unit is mounted within a stainless steel enclosure with removable cover panel. Valve bonnets, dial thermometer and the outlet project outside the enclosure. The hose and rack are mounted outside the enclosure. All water and steam piping is concealed.

Optional Recessed Wall Full Unit Enclosure Mixing unit and discharge hose are mounted within a stainless steel enclosure with hinged door. Water and steam piping, valves, and dial thermometer are concealed.



Page 9

Ph: (800) 554-1394

ARCHON Industries, Inc. 357 Spook Rock Road, Suffern NY 10901

Fax: (845) 368-3040